

LiNX electronics system further increases your mobility









Mobility and freedom of choice with the REAL 6100 PLUS LiNX

When your legs are weak, you need a chair to both sit in and move around with. The chair must be easy to manoeuvre wherever you want. The new LiNX Control System provides improved customised driving features.

Easily manoeuvrable electric wheelchair for maximum mobility

The REAL 6100 PLUS LiNX is a 6-wheel electric wheelchair for indoor use. The chair can be individually adapted for people of all ages. The very narrow chassis, along with centre-wheel drive, makes it easy to move around in confined spaces. The electrically adjustable seat height range is 28 cm, which enables the user to reach heights not usually reachable for a seated person. And our extra-low electric lifting device allows for a seat height as low as 33 cm. Along with the new LiNX Control System from Dynamic Controls, this gives the user maximum mobility, both horizontally and vertically, at home or in school.

LiNX Control System provides a safer driving experience

The REAL 6100 PLUS LiNX offers a variety of customisation options. The controller is easy to understand and user-friendly. Drive features, which can be easily personalised in real-time via Bluetooth, provides the user with an even better and safer driving experience. LiNX Control System simplifies both use and customisation, as well as service.

Freedom of choice

The REAL 6100 PLUS LiNX is highly adaptable to the unique needs and preferences of the user. The standard version has an ergonomically seating system and folding armrests to allow easy sideways transfer into and out of the chair. The legrest has a stable foot plate and is adjustable for height and angle. LiNX Control System is compatible with external suppliers' control units and can be programmed with up to 20 different electric functions.

A wide range of options and accessories

The REAL 6100 PLUS LiNX offers a wide range of options and accessories. You can choose between different types of seat and backrest tilts, various seats and backrests, as well as numerous accessories to optimise customisation. For more information, please visit our WEBguide/shop where you can build your own chair shop.mercado.se, or contact us.

We are proud to offer Dynamic Controls' wide selection of electronic accessories for LiNX Control System for even better customisation. You can find more information at dynamiccontrols.com





A system where your needs determine the design

Benefits of LiNX Control System

- The LiNX controller is easy to understand and user-friendly
- LiNX is an expandable module system
- LiNX is compatible with external supplier control units
- The LiNX system has a built-in gyro for increased safety and a better driving experience
- LiNX internal logging system saves history in chronological order
- Drive features can be wirelessly customised in real-time while driving - also simplifies service
- Same power module regardless of configuration and complexity
- Automatic reading and compensation of motors for a better driving experience



TECHNICAL DATA

135 kg Max user weight 4.5 km/h Max speed Turning space 180° 870 mm Drive wheel both centre wheels Driving distance per charge approx. 15 km

Obstacle ability Weight Charging time

Charger tested and approved by Mercado Medic AB

Battery tested and approved by

Mercado Medic AB Sonnenschein 2st 12V 25 Ah

STANDARD MEASUREMENTS

Total width 570 mm 795 mm Length Wheel front/back Ø 125 mm Drive wheel Ø 210 mm

Seat height 460-740 mm*, 380-580 mm*, 330-480 mm

Legrest length 370-530 mm Seat width 290-480 mm Seat depth 320-530 mm

-15° +8°, -8° +15°, 0° +23° Seat tilt

Backrest height 330-430 mm Backrest tilt -15-+45°

* Possible stepless downward adjustment of max 3 cm. Measured without seat tilt from floor to seat underside with seat in flat position.
With seat tilt +1 cm. With seat tilt "adjustable reinforced seat frame" +2 cm.

PROGRAMMING OPTIONS

Choice of different programmable functions:

- Forward speed
- Forward acceleration
- Forward braking distance
- Reverse speed
- Reverse acceleration
- Reverse braking distance
- Turning speed

40 mm

76 kg incl. battery

Mentzer 2,5A, ECB-801

approx. 6-8 hrs

Easy buddy 4A

- Turning acceleration
- Turning deceleration
- Joystick sensitivity
- · Use of external joystick
- · Reverse joystick function



MERCADO TAILORS YOUR CHAIR TO MEET YOUR UNIQUE NEEDS. **GO TO OUR WEBGUIDE** AND BUILD YOUR OWN CHAIR!**

"shop.mercado.se

CE



Mercado Medic AB Tryffelslingan 14 181 57 Lidingö, Sweden Fax

Phone & Fax Phone + 46 8 555 143 00 +46 8 555 143 99

E-mail & Internet E-mail info@mercado.se

Internet www.mercado.se